



The CodaAir® Lineup

for IVF Laboratories

...The Ultimate VOC Filtration Technology for IVF

All products in the CodaAir® Lineup are clinically proven for safe and effective use in human ART laboratories. The ultimate effective air technology to purify volatile organic compounds and pollutants.

Our High Performance™ 4-Stage Filter® system has been proven to improve air quality in laboratories and may increase expected outcome and overall results. Coda® products have protected IVF laboratories for over 18 years and have shown a superior performance record.

Coda® ECO™ Towers offer large capacity purification with our efficient 4-Stage Filter System



ECO™ 1200

| | |
|-----------------------------|-------------------------------|
| Catalogue #: 115V 230V | GELT-001/115 GELT-001/230 |
| Coverage: sq. ft. sq. m. | 800 – 1800 74 – 167 |
| Air exch. per hour | 8 – 27 times |
| Size dXwXh: in cm | 13 x 18 x 54 33 x 46 x 137 |
| Weight: pounds kilograms | 120 54 |
| Change Filters As Scheduled | |
| Initial Filter Kit | GEIK-1200 |
| Semi-Annual Kit | GESA-1200 |
| Annual Kit | GEAK-1200 |

ECO™ 1500

| | |
|-----------------------------|---------------------------------|
| Catalogue #: 115V 230V | GECO-009/115 GECO-009/230 |
| Coverage: sq. ft. sq. m. | 1000 – 2400 92 – 223 |
| Air exch. per hour | 5 – 22 times |
| Size dXwXh: in cm | 13.5 x 18 x 73 34 x 46 x 185 |
| Weight: pounds kilograms | 135 61 |
| Change Filters As Scheduled | |
| Initial Filter Kit | GEIK-1500 |
| Semi-Annual Kit | GESA-1500 |
| Annual Kit | GEAK-1500 |



Tower 2000

| | |
|-----------------------------|-------------------------------|
| Catalogue #: 115V 230V | GTTU-040/115 GTTU-040/230 |
| Coverage: sq. ft. sq. m. | 1200 – 2500 111 – 232 |
| Air exch. per hour | 6 – 25 times |
| Size dXwXh: in cm | 13 x 25 x 73 33 x 64 x 185 |
| Weight: pounds kilograms | 180 81.65 |
| Change Filters As Scheduled | |
| Initial Filter Kit | CCTI-081 |
| Semi-Annual Kit | CCTS-081 |
| Annual Kit | CCTA-081 |

CodaAir® 900

| | | |
|-----------------------------|-------------------------------|-------------------------|
| Catalogue #: | A900-009 | |
| 24V Universal Adapter | | |
| Coverage: sq. ft. sq. m. | 900 – 1100 83 – 102 | |
| Air exch. per hour | 5 – 25 times | |
| Size dXwXh: in cm | 12 x 18 x 45 30 x 46 x 114 | |
| Weight: pounds kilograms | 75 34 | |
| Filters | | |
| | Choice A (shiribox) | Choice B (canisters) |
| Initial Filter Kit | included | CCFK-900 |
| Semi-Annual Kit | CAFK-900 (2pk) | CCSK-900 |
| Annual Kit | n/a | CCFK-900 |




4-Stage Filter System More Carbon...Better Results

Initial Filter Kit



Install with initial set-up of tower.

Semi-Annual Kit



Change 6 months after annual kit.

Annual Filter Kit



Change 6 months after semi-annual kit.



www.CodaAir.com



The Aero® Series are Small, Compact, Versatile Units



Aero® 400

| | |
|--------------------------------------|------------------------------------|
| Catalogue #: 115V 230V | A400-001/115 A400-001/230 |
| Coverage: sq. ft. sq. m. | 300 – 500 28 – 46 |
| Air exch. per hour | 9 – 12 times |
| Size dXwXh: in cm | 16 diam x 22 41 diam x 56 |
| Weight: pounds kilograms | 45 20 |
| Change Filters Every 3 Months | |
| Initial Filter Kit | Included |
| Quarterly Kit | GCAF-001 (1 pk) GCAF-002 (2 pk) |

Aero® 500

| | |
|--------------------------------------|------------------------------------|
| Catalogue #: 115V 230V | GCAU-010/115 GCAU-010/230 |
| Coverage: sq. ft. sq. m. | 300 – 600 28 – 55 |
| Air exch. per hour | 8 – 14 times |
| Size dXwXh: in cm | 16 x 16 x 25 41 x 41 x 64 |
| Weight: pounds kilograms | 50 23 |
| Change Filters Every 3 Months | |
| Initial Filter Kit | Included |
| Quarterly Kit | GCAF-001 (1 pk) GCAF-002 (2 pk) |



Aero® 700

| | |
|--------------------------------------|------------------------------|
| Catalogue #: 115V 230V | A700-007/115 A700-007/230 |
| Coverage: sq. ft. sq. m. | 500 – 700 46 – 65 |
| Air exch. per hour | 4 – 22 times |
| Size dXwXh: in cm | 12 x 18 x 26 30 x 46 x 66 |
| Weight: pounds kilograms | 52 24 |
| Change Filters Every 6 Months | |
| Initial Filter Kit | Included |
| Semi-Annual Kit | GCAF-702 (2 pk) |

CodaAir® 800

| | |
|---------------------------------------|------------------------------|
| Catalogue #: 24V Universal Adapter | A800-008 |
| Coverage: sq. ft. sq. m. | 500 – 700 46 – 65 |
| Air exch. per hour | 4 – 22 times |
| Size dXwXh: in cm | 12 x 18 x 26 30 x 46 x 66 |
| Weight: pounds kilograms | 52 24 |
| Change Filters Every 6 Months | |
| Initial Filter Kit | Included |
| Semi-Annual Kit | CAFK-800 (2 pk) |




Aero® Filters



Round Filters

For the Aero® 400 & 500 models.
Change every 3 months.
Sold as singles or in a 2 pack.



Square Shirtbox Filters

For the Aero® 700 and the
CodaAir® 800 & 900 models.
Change every 6 months.
Sold only in a 2 pack.



Coda® Filters and Coda® Xtra Inline® Filters

More Carbon...Better Results

Coda® Filters for All Coda® Units & SP Units

Change every 30 days.

Cat #: GCIF-006 (6 pk)
GCIF-012 (12 pk)



Coda® Unit
Cat #: GCIU-010

Coda®2 Unit
Cat #: C2IU-010
Kit: C2KT-107

Coda®2 SP
Cat #: C2SP-010

Coda® SP
Cat #: GCSP-010

Coda® Xtra Inline® Filters

Attach to your incoming gas lines.

For Best Results, change filters every
3 months or when cylinders are
replaced (can be used up to 6 months).

Coda® Xtra Inline® Green with AldaSorb®

Cat #: CXGR-006 (6 pk)
CXGR-012 (12 pk)

Coda® Xtra Inline® Blue

Cat #: CXBL-006 (6 pk)
CXBL-012 (12 pk)

